

IPA Wipe

IPA Wipe offer a precise solution for professionals who prioritize cleanliness and safety when working with electronics and optics. Soaked in 99.9% pure isopropanol, they effectively remove grease, dust, and other contaminants without damaging delicate surfaces. Thanks to their compact size, these wipes are perfect for reaching hard-to-access areas, ensuring flawless results without leaving any residue.

Product features:

- ✓ exceptional cleaning effectiveness,
- ✓ high durability,
- ✓ versatile applications,
- ✓ chemically neutral,
- ✓ long-lasting moisture retention due to special packaging,
- ✓ streak-free finish.

Application:

- ✓ touchscreens and displays in smartphones, tablets, monitors,
- ✓ camera lenses, optical equipment,
- ✓ keyboards, mice, and other peripherals,
- ✓ PCBs and soldering componentse,
- ✓ AV mechanisms and heads,
- ✓ fiber optic connectors,
- ✓ precision tools in service centers and laboratories.



Physicochemical properties

Appearance	Wipe
Odour	Characteristic
Color	White
Density of isopropanol at 20°C	Min. 0.79 g/cm ³
Acidity of isopropanol as acetic acid content	Max. 0.01%
Dimensions	16 × 12.5 cm
Shelflife	2 years

Compatibility:

IPA Wipes are chemically neutral to most materials, allowing them to be safely used on various surfaces – from delicate touch screens, optical lenses, to housing components and precision mechanisms. The neutrality of the formula prevents damage, corrosion, and unwanted aesthetic changes, making the wipes perfect for the maintenance and cleaning of electronic and optical equipment in various conditions and work environments.

Application method	
Wipe	Yes

Usage instructions:

Restricted to professional users. Read safety data sheet carefully prior to use.

Ensure the device is turned off. Open the sachet containing the single IPA Wipe, and gently wipe the device's surface. With dimensions of 16 x 12.5 cm, the wipe is perfectly suited for both larger surfaces and hard-to-reach areas. The product is packaged in sachets, with each sachet ensuring the wipe's freshness and effectiveness.

Package	
Cardboard box	25 sachets (ART.AGT-181) - 1/20 pcs.*

*Quantity of pcs. in a bulk package

Storage:

Store in a well-ventilated, cool and dry place.

Technical support:

AG TermoPasty provides technical support, answering questions about the technical specifications and applications of our products. Please contact us via email at info@termopasty.pl.

Note:

The data presented in this document reflect our current state of knowledge and describe the typical properties and applications of the product. However, the responsibility for determining the suitability of this product for specific applications lies with the user. AG TermoPasty is not liable for the results of the product's use, as the conditions of its application are beyond our control.

